


In questa postazione di lavoro trovano facile collocazione l'iniettore sottovuoto IC30EVO, la morsa pneumatica, il compressore silenzioso e la pompa del vuoto. Sopra l'iniettore è posizionata una lampada a luce bianca orientabile. Grazie alla cassetteria laterale e al ripiano superiore si possono facilmente riporre le gomme da iniettare e ogni altro oggetto utile; è inoltre previsto un ripiano laterale estraibile che amplia lo spazio utile disponibile. Sono inoltre disponibili due prese di corrente e una uscita per aria compressa per la pulizia delle gomme dai residui di cera.

This workstation can include a vacuum injector IC30EVO, a pneumatic-operated vice, a silenced compressor and a vacuum pump. A whitelight, movable lamp is placed over the injector. A side chest of drawers and a top shelf allow for the preservation of rubber to be injected and any other useful tool; a side, pull-out shelf widens the working space available. Two outlets and a compressed-air outlet are available in order to clean rubber from wax residues.



Articolo	Dimensioni mm	
BC30EVO	1040 x 740 x 1500h	Kg 60